

**Diamond dished grinding wheel D×T×H (mm), 125×23×20, Type: D151****Order data**

Order number	597750 D151
GTIN	9003177313998
Item class	53Y

**Description****Version:**

**Cup grinding wheels and dished grinding wheels with diamond abrasive coating.** Coarse-grained for the best metal removal rates. **Specification: D151C75B DIAGO W-Carbide.**

**Application:**

**For general use on all common tool grinding machines.** For grinding **carbide tools and short chipping non-ferrous materials.** Very well suited to dry grinding, but can also be used for wet grinding.

**Technical description**

Grit	D151
Specification	D151C75B DIAGO W-Carbide
Grinding medium code	D
Grinding process	Tool grinding
Grinding media	Diamond
Shape	12A2F

Disc Ø D	125 mm
Disc thickness T	23 mm
Product name attribute	125×23×20
Bore Ø H	20 mm
Abrasive coating width W end face	5 mm
Abrasive coating height X	4 mm
Type of product	Sanding pad

### User data

	Suitability	V <sub>c</sub>	ISO code
Carbide (HM)	suitable		
Plastic, GRP	suitable only under restricted conditions		
wet maximum	suitable only under restricted conditions		
dry	suitable		