



Diamond cutting disc D×T×H (mm), 75×0.8×20, Type: D126



Order data

Order number	598590 D126
GTIN	9003171578003
Item class	53Y

Description

Version:

High performance cutting disc with diamond coating in synthetic resin bonding with very long working life and high cutting performance.

Specification: D126C75B-Carbide.

Application:

- **Cutting carbide on stationary cutting grinding machines.**
- **Wet cutting is preferred (working life, temperature, performance).**
- **Working speed 20–40 m/s.**

Shape: 1A1R

Abrasive coating height X: 5 mm

Technical description

Grit	D126
Specification	D126C75B tungsten carbide
Grinding process	Cutting
Grinding media	Diamond

Grinding medium code	D
optimised for material	Carbide
Shape	1A1R
Disc Ø D	75 mm
Disc thickness T	0.8 mm
Product name attribute	75×0.8×20
Bore Ø H	20 mm
Abrasive coating width U	0.8 mm
Abrasive coating height X	5 mm
Propulsive equipment	Stationary cutting machines
recommended circumferential speed	20 - 40 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Carbide (HM)	suitable		
Plastic, GRP	suitable only under restricted conditions		
Stone	suitable only under restricted conditions		
wet maximum	suitable		
dry	suitable only under restricted conditions		