

**Adjustable caliper pin wrench cranked, Pin nominal Ø: 5mm****Order data**

Order number	628610 5
GTIN	4020772050931
Item class	63Q

Description**Version:**

Special steel, drive head ground, hardened and burnished; with fixed pins.

Application:

For twin hole nuts.

Note:

Pin Ø = pin nominal Ø - 0.1 mm. Tolerance zone h12.

Technical description

Pin spacing adjustable a	14 - 90 mm
Pin nominal Ø	5 mm
Type	758
Manufacturer's designation	758CC
Length L	205 mm
swan necked	yes
flat	no
adjustable for width	yes
Type of product	Pin spanner

