


Garant
TCGW 16T308, BU7220, Cutting edge version: G

Order data

| | |
|--------------|---------------|
| Order number | 265454 G |
| GTIN | 4045197895677 |
| Item class | 21H |

Description
Version:

Fitted with 3 cutters.

Grade: BU7220

Cutting edge version: G

Cutting depth a_p : 0.03 - 0.12 mm

Feed f : 0.04 - 0.12 mm/rev.

Cutting speed v_c main application: 120 - 160 m/min

Technical description

| | |
|--------------------------------------|----------------------|
| Cutting speed v_c main application | 120 - 160 m/min |
| Grade | BU7220 |
| Cutting edge version | G |
| Cutting depth a_p | 0.03 - 0.12 mm |
| Cutting conditions | heavily interrupted |
| Cutting conditions | slightly interrupted |
| Cutting conditions | continuous |

| | |
|-------------------------------|------------------------------|
| Feed f | 0.04 - 0.12 mm/rev. |
| Corner radius | 0.8 mm |
| Tool material | CBN |
| Finishing/roughing assignment | Finishing |
| ISO code indexable insert | TCGW 16T308 |
| Number of changes/inserts | 3 |
| Product name attribute | BU7220 |
| Type of product | Indexable insert for turning |

User data

| | Suitability | V _c | ISO code |
|----------------|-------------|----------------|----------|
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| continuous | suitable | | |
| irregular | suitable | | |
| interrupted | suitable | | |
| dry | suitable | | |