

“Go” / “No Go” plug gauge with numerical tolerance with wear allowance, Type: K



Order data

| | |
|--------------|---------------|
| Order number | 484026 K |
| GTIN | 2050001952554 |
| Item class | 48B |

Description

IMPORTANT: item is configurable

Tolerance zone: A; B; C; CD; D; E; EF; F; FG; G; H; J; JS; K; M; N; P; R; S; T; U; V; X; Y; Z; ZA; ZB; ZC

Quality: 10; 11; 12; 13; 6; 7; 8; 9

Nominal size: 90.001 - 99.999 mm, Intervall: 0,001

Version:

Measuring body made of first class gauge steel, hardened, stress-relieved, ground, and lapped.

The “Go” ends of these working gauges have a wear allowance to DIN 7164.

“Go” / “No Go” plug gauge with numerical tolerance, e.g. 484026 **28 + 0.01 / - 0.02**.

Standard:

Toleranz und Abmaße nach **DIN 1938-1, DIN 2245-1 und DIN 7164**.

Note:

- **Please state the exact nominal \varnothing with tolerance band (A-ZC) and quality (6-13) or numeric tolerance (\pm).**
- **Intermediate size plug gauges are just double-ended plug gauges in fractional sizes!**
- **For whole number (even) \varnothing with ISO fits see No. 484000; 484020; 484040 or on request.**
- **For acceptance gauges (without wear allowance) see No. 484027; 484028.**

Calibration: L6

Nominal size: 90.001 - 99.999 mm

Technical description

| | |
|----------------|---|
| Tolerance zone | A |
| Tolerance zone | G |
| Tolerance zone | H |

| | |
|-----------------|-------------------|
| Tolerance zone | J |
| Tolerance zone | K |
| Tolerance zone | M |
| Tolerance zone | N |
| Tolerance zone | P |
| Tolerance zone | R |
| Tolerance zone | S |
| Tolerance zone | B |
| Tolerance zone | T |
| Tolerance zone | U |
| Tolerance zone | V |
| Tolerance zone | X |
| Tolerance zone | Y |
| Tolerance zone | Z |
| Tolerance zone | ZA |
| Tolerance zone | C |
| Tolerance zone | D |
| Tolerance zone | E |
| Tolerance zone | F |
| Tolerance zone | JS |
| Tolerance zone | CD |
| Tolerance zone | EF |
| Tolerance zone | FG |
| Tolerance zone | ZC |
| Tolerance zone | ZB |
| Tolerance value | -2.7 - 5.4 |
| Standard | DIN 7164 |
| Standard | DIN 2245-1 |
| Standard | DIN EN ISO 1938-1 |

| | |
|-----------------|--------------------|
| Quality | 13 |
| Quality | 9 |
| Quality | 8 |
| Quality | 10 |
| Quality | 6 |
| Quality | 11 |
| Quality | 7 |
| Quality | 12 |
| Type of gauge | "Go" plug gauge |
| Type of gauge | "No Go" gauge |
| Nominal size | 90.001 - 99.999 mm |
| Calibration | L6 |
| Type of product | Pug Gauge |

Services

| | |
|--|------------|
| Labelling laser-etched Type | 018940 |
| Calibration "Go" / "No Go" plug gauge maximum Ø 200 mm | 018400 200 |
| DAkkS calibration "Go" / "No Go" plug gauge maximum Ø 200 mm | 019620 200 |
| Calibration "Go" / "No Go" plug gauge maximum Ø 200 mm | 028300 200 |
| DAkkS calibration "Go" / "No Go" plug gauge maximum Ø 200 mm | 028340 200 |