

Acceptance gauges with numerical tolerance without wear allowance, Type: F



Order data

Order number	484028 F
GTIN	2050001952721
Item class	48B

Description

IMPORTANT: item is configurable

Tolerance zone: A; B; C; CD; D; E; EF; F; FG; G; H; J; JS; K; M; N; P; R; S; T; U; V; X; Y; Z; ZA; ZB; ZC

Quality: 10; 11; 12; 13; 6; 7; 8; 9

Nominal size: 24.001 - 30 mm, Intervall: 0,001

Version:

Measuring body made of first class gauge steel, hardened, stress-relieved, ground, and lapped. Acceptance gauges are made with no wear allowance at the "Go" end.

Acceptance gauges with numerical tolerance, e.g. 484028 **28 + 0.01 / - 0.02**.

Note:

- **Please state the exact nominal \varnothing with tolerance band (A-ZC) and quality (6-13) or numeric tolerance (\pm).**
- **Intermediate size plug gauges are just double-ended plug gauges in fractional sizes!**

Calibration: L6

Nominal size: 24.001 - 30 mm

Technical description

Tolerance zone	A
Tolerance zone	G
Tolerance zone	H
Tolerance zone	J
Tolerance zone	K
Tolerance zone	M
Tolerance zone	N

Tolerance zone	P
Tolerance zone	R
Tolerance zone	S
Tolerance zone	B
Tolerance zone	T
Tolerance zone	U
Tolerance zone	V
Tolerance zone	X
Tolerance zone	Y
Tolerance zone	Z
Tolerance zone	ZA
Tolerance zone	C
Tolerance zone	D
Tolerance zone	E
Tolerance zone	F
Tolerance zone	JS
Tolerance zone	CD
Tolerance zone	EF
Tolerance zone	FG
Tolerance zone	ZC
Tolerance zone	ZB
Tolerance value	-1.65 - 3.3
Standard	DIN 7164
Standard	DIN 2245-1
Standard	DIN EN ISO 1938-1
Quality	12
Quality	11
Quality	9
Quality	10

Quality	6
Quality	8
Quality	7
Quality	13
Nominal size	24.001 - 30 mm
Type of gauge	Acceptance plug gauge
Calibration	L6
Type of product	Pug Gauge

Services

Labelling laser-etched Type	018940
Calibration "Go" / "No Go" plug gauge maximum \varnothing 60 mm	018400 60
DAkkS calibration "Go" / "No Go" plug gauge maximum \varnothing 60 mm	019620 60
DAkkS calibration "Go" / "No Go" plug gauge maximum \varnothing 60 mm	028340 60
Calibration "Go" / "No Go" plug gauge maximum \varnothing 60 mm	028300 60