



Precision circlip pliers set for internal and external circlips, Number of pliers: 4



Order data

Order number	700155 4
GTIN	4003773050056
Item class	73F

Description

Version:

Forged grip and joint, precision made tips of special steel, special precision profile, pressed into the body. Pliers black, head ground, plastic coated handles.

Joint for external ring pliers with **integral opening spring**.

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Standard:

DIN 5256 C und D – für Innensicherungsringe.

DIN 5254 A und B – für Außensicherungsringe.

Supplied with:

1 each retaining ring pliers No. 719790 size J1 and J2.

1 each retaining ring pliers No. 719890 size A1 and A2.

Technical description

maximum overall length of external circlip pliers	140; 185 mm
Tip Ø for external circlip pliers	1.25; 1.8 mm
maximum overall length of internal circlip pliers	140; 180 mm

Number of pliers	4
Tip Ø for internal circlip pliers	1.25; 1.8 mm
for external circlip Ø	10 – 25; 19 – 60 mm
for internal circlip Ø	12 – 25; 19 – 60 mm
Use of circlip pliers	Outer ring, straight
Use of circlip pliers	Inner ring, straight
Storage in	Textile roll-up case
Standard	DIN 5254 A and B
Standard	DIN 5256 C and D
Type of product	Circlip Pliers

Accessories

Precision circlip pliers Type A2	719890 A2
Precision circlip pliers Type J2	719790 J2
Precision circlip pliers Type A1	719890 A1
Precision circlip pliers Type J1	719790 J1