

**Garant****Circular saw blade, trapezoidal flat teeth INOX, Blade Ø D: 305mm****Order data**

Order number	584004 305
GTIN	4045197883728
Item class	51S

**Description****Version:**

**Tipped with carbide inserts**, precision version with high-strength blade, noise damped. Generously dimensioned carbide teeth allow multiple re-grinding.

**Application:**

**Universal saw blade** for machining **stainless steel** with crosscut and mitre saws. Problem-free cutting off of pipes, sheet metal, profiles and solid material. Suitable for both steel and non-ferrous materials. Not suitable for cast iron. Low-burr, quick cutting without cooling.

**Technical description**

Number of teeth	72
Tooth version	Trapezoidal flat teeth
Width of cut B	2.2 mm
Bore Ø	25.4 mm
Blade Ø D	305 mm
Type of product	Circular saw blade

