


Garant

Fixed solid carbide lathe centre 60° with push-off thread, very large Ø / Morse taper: 70/4



Order data

Order number	323210 70/4
GTIN	4045197883797
Item class	31Z

Description

Version:

- **High-precision solid carbide tip. Close-fitting carbide design for optimum stability and freedom from breakage, no additional safety equipment required.**
- **Tip angle 60°.**
- **High surface quality on the shank for optimum fit.**
- **Complete tool hardened and ground.**
- **With carbide tips for applications with high wear.**

Description:

Lathe centres are mainly used on lathes to support long and slim workpieces, since with these workpieces there would otherwise be a risk of the workpiece bending or moving around as a result of the forces generated.

The lathe centre is secured with a Morse taper. The workpiece is clamped in the chuck and a counterbore is added using a centre drill. After re-clamping, the lathe centre is then inserted.

Application:

For grinding high-precision components.

Optional extras:

Draw-off nut No. 323230.

Note:

Order the draw-off nut separately. Geometric dimensions to DIN 806 E.

Head length L: 72.5 mm

External Ø D: 70 mm

Ø d: 55 mm

maximum radial run-out: 0.001 mm

Thread M: M36x1.5

Technical description

Morse taper	4
External Ø D	70 mm
Ø d	55 mm
maximum radial run-out	0.001 mm
Thread M	M36×1.5
Head length L	72.5 mm
Type of product	Centring drill

Accessories

Draw-off nut Type M36	323230 M36
-----------------------	------------