

Garant**Gripp insert, Type: 7****Order data**

Order number	361160 7
GTIN	2050001919250
Item class	34A

Description**Application:**

Serrated gripp insert, e.g. to clamp blanks. Smooth clamping insert with coating, e.g. for clamping pre-machined components. Serrated gripp insert, round, for drilling near to edges and for additional clearance under the workpiece.

For workpieces with a large radius or chamfer between 3 and 8 mm. For workpieces with a large radius or chamfer between 3 and 8 mm.

Suitable for:

Gripp top jaw No. 361128 – 361129.

Allmatic jaws No. 361206 – 361354. GARANT Xpent top jaws No. 361128 and 361129. GARANT Xtric top jaw 363038 125.

Technical description

Height	8 mm
Version	round
Type of product	Gripp insert

