

FLUKE.

Clamp meter, Type: 325**Order data**

Order number	473290 325
GTIN	095969623766
Item class	47H

Description**Version:**

Current clamps with large easy-to-read LCD display in a slim and ergonomic design. Additionally temperature measurement, frequency measurement, min/max function and display with backlight.

True effective value measurements and optimised ergonomics for troubleshooting in industrial and building technology applications.

Standard:**EN 61010-1****Supplied with:**

Incl. test leads and padded carrying case. Batteries 2 pcs. No. 081561 size LR3.

Technical description

AC voltage	0.1 V – 600 V
Overvoltage category	CAT III 600 V
Overvoltage category	CAT IV 300 V
maximum jaw aperture	30 mm

Capacitance	100.0 μ F up to 1000 μ F
DC voltage	0.1 V – 600 V
Measurement process	TRUE RMS (AC)
DC current	0.1 A - 400 A
Frequency	5 Hz – 500 Hz
Information displayed	4000
AC current	0.1 A - 400 A
Memory function	HOLD, MAX/MIN
Basic accuracy	2 %
Resistance	0.1 Ω – 40 k Ω
Contact measurement of temperature	-10 - 400 $^{\circ}$ C
Article no of the battery / rechargeable battery fitted	081561 LR3
Number of batteries contained	2
Power supply	Battery-powered
Power supply	2 \times 081561 LR3
Standard	EN 61010-1
Calibration	I4
Type of product	Current clamp

Services

DAkkS calibrationClamp meter Type D	027060 D
CalibrationClamp meter Type D	027050 D

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------