

HOLEX**Grooving tool right-hand, similar to DIN 4981 (ISO 7), M20, Shank height: 12mm****Order data**

Order number	297030 12
GTIN	4045197885531
Item class	22E

Description**Version:**

Fitted with diamond ground carbide inserts.

Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Technical description

Blade width	3 mm
Shank height h	12 mm
Overall length	100 mm
Shank width b	8 mm
Tool material	M20
Type of product	Turning tool