



Hook turning tool right-hand, similar to DIN 263 (ISO 11), M20, Shank square: 25mm



Order data

Order number	297145 25
GTIN	4045197885630
Item class	22E

Description

Version:

Fitted with diamond ground carbide inserts.

Application:

P20/K25 for machining steel and cast iron.

M20 for machining stainless steels.

Attention:

For rough and interrupted machining the cutting edges should be sharpened with a boron carbide hand lapper (No. 558812).

Technical description

for bores from \varnothing	60 mm
Blade width	8 mm
Shank square	25 mm
maximum grooving depth t_{\max}	20 mm
Overall length	250 mm
Tool material	M20
Type of product	Turning tool