

Garant
GARANT Master Tap machine tap HSS-E-PM, ALTiX, UNF: 7/16-20

Order data

Order number	133410 7/16-20
GTIN	4045197901859
Item class	111

Description
Version:

GARANT Master Tap general-purpose tap, designed for use on a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for maximum wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

Application:

For UNF unified fine threads ASME – B1.1.

Thread type: UNF

Tool material: HSS E PM

Standard: DIN 374

Threads per inch: 20

Thread Ø: 11.11 mm

Overall length L: 100 mm

Shank Ø D_s: 8 mm

Shank square □: 6.2 mm

Tapping hole Ø: 9.9 mm

Technical description

Thread depth	33.33 mm
Tool material	HSS E PM
Shank square □	6.2 mm
Overall length L	100 mm

Standard	DIN 374
Number of cutting edges Z	3
Tapping hole Ø	9.9 mm
Thread Ø	11.11 mm
Thread pitch	1.59 mm
Threads per inch	20
Number of clamping slots	3
Shank Ø D _s	8 mm
Thread type	UNF
Thread size	7/16-20 UNF
Series	Master Tap
Coating	AlTiX
Flank angle	60 °
Tolerance class	2BX
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N

Steel < 500 N/mm ²	suitable	30 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
INOX < 900 N/mm ²	suitable	10 m/min	M
INOX > 900 N/mm ²	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		