

KERN**Hanging scales type HCB, maximum weighing range: 1000kg**

Order data

Order number	479435 1000
GTIN	4045761152762
Item class	47D

Description

Version:

- **Simple operation with 3 buttons.**
- **With tare button, attach empty container and set indication to zero.**
- **Hold button, the indication can be frozen for 5 seconds.**
- **Display unit switchable between kg, N and lb.**

Supplied with:

Stainless steel carabiner, stainless steel S-hook (non-standard for size 500 / 1000) and 3 batteries No.081561 size LR6.

Optional extras:

Shackle and hook with safety lock on request.

Technical description

Body width	80 mm
Scale divisions	2000 g
Net weight	0.55 kg
Body height	150 mm

Calibration	Price on request
maximum weighing range	1000 kg
Body depth	48 mm
Article no of the battery / rechargeable battery fitted	081561 LR6
Number of batteries contained	3
Power supply	Battery-powered
Manufacturer's designation	HCB
Type of product	Suspended scales / crane scales

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
---	------------