



## Tool24 Smartline – upright cabinet fitted with tool sockets, for tool shanks: C5



### Order data

Order number	979100 C5
GTIN	4045197885920
Item class	9SA

### Description

#### Version:

Flexible goods issuing system for storage and management of machining and assembly tools, measuring tools, protective work-wear and many other consumable items. Master systems can be extended using the optional extension cabinets (slave system). The individual software packages allow the systems to be tailored to your exact requirements.

The pull-out shelves are supported from the base and equipped with central locking. (Can be used for emergency unlocking). The end faces of the hot-dip galvanised frames of the pull-out shelves have holes at intervals of 37 mm for mounting tool carriers, carrying rails, storage shelf trays, and perforated tool boards. The pull-out frames are equipped with an anti-tilt device. The pull-out frames open automatically. This ensures quick access to the tools.

#### Application:

Automatic goods issuing system for storage and management of tools and accessories.

#### Colour:

Body light grey RAL 7035, pull-out frames signal blue RAL 5005, **powder-coated**.

#### Note:

Upright cabinets can be set up only on ground that is absolutely level. They are prepared for wall or floor-mounting and must be secured against tilting. These upright cabinets can be used only in conjunction with a Tool24 Smartline Master System 979000 S11M or 979000 S11M-EN.

Colour selection: RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003

Vertical pull-out frame load capacity: 600 kg

Height: 2000 mm  
 Width: 717 mm  
 Depth: 750 mm  
 Pull-out frame drawers width: 155 mm  
 Vertical pull-out frame usable height: 1750 mm  
 Number of pull-out frames: 4

## Technical description

Weight	320 kg
Height	2000 mm
Width	717 mm
Depth	750 mm
Pull-out frame drawers width	155 mm
Number of pull-out frames	4
Vertical pull-out frame load capacity	600 kg
Vertical pull-out frame version	supported from the base
Number of tool sockets	192
Number of tool carriers No. 970130	24
Axial spacing A	82 mm
Vertical pull-out frame usable height	1750 mm
Cabinet housing internal load capacity	2400 kg
Drawer runner extension	Anti-tilt lock
Cylinder lock	modular lock barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Tool issuing system