

Garant
GARANT Master Tap machine tap HSS-E-PM, ALTiX, UNC: 3/4-10

Order data

Order number	133360 3/4-10
GTIN	4045197901736
Item class	111

Description
Version:

GARANT Master Tap universal taps, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for maximum wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

Application:

For UNC uniform coarse threads ASME – B1.1.

Thread type: UNC

Tool material: HSS E PM

Standard: DIN 376

Threads per inch: 10

Thread Ø: 19.05 mm

Overall length L: 125 mm

Shank Ø D_s: 14 mm

Shank square □: 11 mm

Tapping hole Ø: 16.5 mm

Technical description

Number of clamping slots	3
Tool material	HSS E PM
Number of cutting edges Z	3
Thread type	UNC
Thread pitch	2.54 mm

Shank $\varnothing D_s$	14 mm
Overall length L	125 mm
Thread size	3/4-10 UNC
Thread \varnothing	19.05 mm
Standard	DIN 376
Threads per inch	10
Tapping hole \varnothing	16.5 mm
Shank square \square	11 mm
Thread depth	57.15 mm
Series	Master Tap
Coating	AlTiX
Flank angle	60°
Tolerance class	2BX
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P

Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
INOX < 900 N/mm ²	suitable	10 m/min	M
INOX > 900 N/mm ²	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		