



Torque screwdriver holder, maximum torque: 500cNm



Order data

| | |
|--------------|---------------|
| Order number | 659991 500 |
| GTIN | 2050001922328 |
| Item class | 66F |

Description

Suitable for:

Interchangeable blades for Torx® No. 659995 and Torx Plus® No. 659996 and also set No. 659990.

Technical description

| | |
|---------------------------|--------------|
| maximum torque | 500 cNm |
| Torque range | 60 - 500 cNm |
| Torque measuring accuracy | ±6 % |
| Torque range | 0.6 - 5 Nm |
| Reversible reading | Nm |
| Overall length L | 131.4 mm |
| Measurement process | Torque |
| Feedback | triggering |
| Adjustable trigger value | preset |

| | |
|---------------------------|---------------------------------|
| Connection format | exchangeable blade |
| Trigger principle | mechanical short-travel release |
| Setting the trigger value | preset |
| Series | Dinaplus |
| Direction of tightening | Right-hand tightening |
| Data can be recorded | no |
| Release signalling | haptic |
| Measurement technology | mechanical |
| Torque fixed setting | yes |
| Type of product | Torque screwdriver |