

PecklInghaus**Hand-operated shears, Model: 1BR/5****Order data**

Order number	769930 1BR/5
GTIN	2050001933379
Item class	76L

Description**Version:**

Sturdy shears body of quenched and tempered steel. Moving blade guides free of play (with low friction losses), blades of special tool steel, specially hardened and ground. Lever arm with counterweight spring for protection in the event of accidents, all pivot pins adjustable, all models with steplessly adjustable clamping arm.

With compound action. Cuts sheet metals and round steel bar.

Colour:

Red-brown.

Note:

- **The following specifications are required for subsequent orders of spare blades: Make, model, and, if known, the machine number or accurate scale drawing.**
- **Please note: The indicated cutting performance is a maximum. If sustained use at the maximum cutting performance is required, we recommend the next larger model.**
- **Cutting performance specifications refer to materials of 450 N/mm² tensile strength.**

Technical description

Cutting capacity sheet thickness	up to 5 mm
----------------------------------	------------

Weight	12 kg
Model	1BR/5
Lower blade length	150 mm
Upper blade length	173 mm
Cutting capacity round steel bar Ø	up to 11 mm
Type of product	Cutting pliers

Accessories

Spare blade for sheet metal (upper blade) Model 1BR/5	769932 1BR/5
Lever retaining spring suitable for model 1BR/5	769931 1BR/5
Lever retaining spring suitable for model 1BR5/2	769933 1BR5/2
Spare blade for sheet metal (lower blade) Model 1BR/5	769934 1BR/5