

Peckingham

Hand-operated shears, Model: 1BR/4**Order data**

Order number	769930 1BR/4
GTIN	2050001933362
Item class	76L

Description**Version:**

Sturdy shears body of quenched and tempered steel. Moving blade guides free of play (with low friction losses), blades of special tool steel, specially hardened and ground. Lever arm with counterweight spring for protection in the event of accidents, all pivot pins adjustable, all models with steplessly adjustable clamping arm.

With compound action. Cuts sheet metals and round steel bar.

Colour:

Red-brown.

Note:

- **The following specifications are required for subsequent orders of spare blades: Make, model, and, if known, the machine number or accurate scale drawing.**
- **Please note: The indicated cutting performance is a maximum. If sustained use at the maximum cutting performance is required, we recommend the next larger model.**
- **Cutting performance specifications refer to materials of 450 N/mm² tensile strength.**

Technical description

Cutting capacity sheet thickness	up to 4 mm
----------------------------------	------------

Data sheet

Model	1BR/4
Lower blade length	120 mm
Cutting capacity round steel bar Ø	up to 10 mm
Weight	10.5 kg
Upper blade length	149 mm
Type of product	Cutting pliers

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/769930-1BR/4>