

**click & go cordless drill / driver with exchangeable drill chuck, Type: GSR1215FC****Order data**

Order number	P07223 GSR1215FC
GTIN	3165140847704
Item class	00N

Description**Version:**

Bosch cordless drill / screwdriver

- **Compact, powerful 12 V cordless drill with forward/reverse operation.**
- **Long service life thanks to brushless EC motor (not 070240).**
- **With Electronic Motor Protection (EMP) and Electronic Cell Protection (ECP).**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**
- **Replaceable colour clips to easily identify the device (not 070240).**

Precise operation even where access is difficult due to compact size **with bit holder** or interchangeable **angle drilling attachment or eccentric drilling attachment**. Flexible working thanks to the quick-change system with four different **FlexiClick**-heads. Comfortable to use: Attachments remain for simply setting 16 different positions on the device.

Supplied with:

With transport case, without battery, without charger.

Note:

See No. 073852 ff and 073866 for suitable spare batteries and chargers.

Technical description

typical application	Strong
Speed range 1st speed	0 - 400 min ⁻¹
maximum torque hard	30 Nm
maximum twist drill size Ø in wood	19 mm
Manufacturer's designation	GSR 12V-15 FC
maximum torque soft	15 Nm
Weight	0.8 kg
Quick-clamping chuck range	0 - 10 mm
maximum vibration to EN	< 1.9 m/s ²
Speed range 2nd speed	0 - 1300 min ⁻¹
suitable battery - supplier / battery type / voltage	Bosch 12 V
Motor design	Brushless motor
Battery voltage	12 V
maximum twist drill size Ø in steel	10 mm
Packaging	Modular case (L-Boxx)
Power supply	Rechargeable battery-powered
Type of product	Drill/driver