

Pecklinghaus**Hand-operated shears, Model: 4BR/8****Order data**

Order number	769930 4BR/8
GTIN	2050001933393
Item class	76L

Description**Version:**

Sturdy shears body of quenched and tempered steel. Moving blade guides free of play (with low friction losses), blades of special tool steel, specially hardened and ground. Lever arm with counterweight spring for protection in the event of accidents, all pivot pins adjustable, all models with steplessly adjustable clamping arm.

With compound action. Cuts sheet metals and round steel bar. With geared action. Cuts sheet metals, flat steel bar, round, and square steel bar. The sheet metal blades are also capable of notching or cutting angle section and T-section steel, at right angles or diagonally. Only 2 - 3 movements of the lever are necessary for this.

Colour:

Red-brown.

Note:

- **The following specifications are required for subsequent orders of spare blades: Make, model, and, if known, the machine number or accurate scale drawing.**
- **Please note: The indicated cutting performance is a maximum. If sustained use at the maximum cutting performance is required, we recommend the next larger model.**
- **Cutting performance specifications refer to materials of 450 N/mm² tensile strength.**

Technical description

Weight	47 kg
Cutting capacity square steel bar	up to 18 mm
Upper blade length	186 mm
Cutting capacity round steel bar \varnothing	up to 20 mm
Model	4BR/8
Cutting capacity sheet thickness	up to 8 mm
Lower blade length	175 mm
Type of product	Cutting pliers

Accessories

Lever retaining spring Version RECHTS	769937 RECHTS
Spare blade for sheet metal (lower blade) Model 4BR/8	769934 4BR/8
Spare blade for sheet metal (upper blade) Model 4BR/8	769932 4BR/8