



Smooth rolling tool G, Parallel shank \varnothing 25 mm, \varnothing D: 34mm



Order data

Order number	291556 34
GTIN	4060491000572
Item class	29F

Description

Version:

For use on CNC and conventional lathes, milling and drilling machines.
Stepless adjustment in μm (adjustment range from -0.05 mm to $+0.1\text{ mm}$).

Advantage:

Specially for production use. Maximum productivity due to **feed rates** from $0.05\text{ mm} - 0.3\text{ mm}$ per roll.

Surface quality $R_z < 1\ \mu\text{m}$ possible.

Automatic release during tool withdrawal avoids damage to smooth rolled surface.

Application:

- For mechanical surface finishing.
- For machining all metallic materials up to a tensile strength of 1400 N/mm^2 and a hardness of up to 45 HRC.
- Clockwise machining.
- Up to tolerance class IT8.
- For holes up to $\varnothing 49\text{ mm}$.

Note:

From $\varnothing 10\text{ mm}$ optionally with internal cooling.

Technical description

Nominal \varnothing D	34 mm
Adjustment range	$-0.05 / +0.1\text{ mm}$
Number of rolls	6
Shank \varnothing D _s	35 mm

Usable length L_N	75 mm
Overhang L_A	153 mm
Shank mounting type	Parallel shank \varnothing 25 mm
Type of product	Smooth rolling tool