

**VBW****Mesh cutter, overall length: 950mm**

## Order data

Order number	737200 950
GTIN	4005887426901
Item class	73L

## Description

**Version:**

Powerful special cutter head with compound action for cutting mesh. Drop forged middle section with adjusting screw for precise adjustment of jaws, forged centre stop, painted tubular handles with multi-component grips.

**Application:**

For cutting reinforcement steel mesh and rod up to 1600 N/mm<sup>2</sup> tensile strength.

**Material:**

Special tool steel cutter head, blades induction hardened.

**Spare part:**

Spare jaws No. 737210. Spare screw No. 737220. Spare adjusting screw No. 737230.

**Note:**

When cutting off  $\varnothing$  8mm / 48 HRC the cutters should be set back several times.

## Technical description

overall length	950 mm
for single bars up to 48 HRC and 1600 N/mm <sup>2</sup>	6 mm
for double bars up to 40 HRC and 1200 N/mm <sup>2</sup>	2×8 mm
for single bars up to 40 HRC and 1200 N/mm <sup>2</sup>	9 mm
for single bars up to 19 HRC and 800 N/mm <sup>2</sup>	11 mm
Type of product	Cutting pliers

---

## Accessories

Spare screw set, with nuts 3 pieces Type 950	737220 950
Spare jaws complete with screws overall length 950 mm	737210 950
Spare adjusting screw with bolt Type 950	737230 950