

**Bolt cutter, overall length: 910mm****Order data**

Order number	733300 910
GTIN	4003773066781
Item class	73F

Description**Version:**

Cutter head with compound action and universal jaws. Eccentric screws allow precise and easy adjustment of the blades. Forged centre stop with protective pads; powder-coated tubular handles with multi-component grips.

Application:

For cutting normal and high-tensile steels up to 48 HRC (about 1600 N/mm² tensile strength).

Material:

Head of chrome-vanadium high performance steel, cutting edges additionally induction hardened (approx. 62 HRC).

Spare part:

Spare jaws No. 733350.

Technical description

overall length	910 mm
for round steel bar up to 48 HRC and 1600 N/mm ² up to Ø	9 mm
for round steel bar up to 40 HRC and 1200 N/mm ² up to Ø	10 mm
for round steel bar up to 19 HRC and 800 N/mm ² up to Ø	13 mm
Material	Chrome vanadium high-performance steel
Type of product	Cutting pliers

Accessories

Spare jaws complete with screws overall length 910 mm

733350 910