

# VBW

## UNIBOLT® bolt cutter, overall length: 610mm



### Order data

Order number	733500 610
GTIN	4005887563309
Item class	73L

### Description

#### Version:

Cutter head with compound action and universal jaws. Eccentric screws allow precise and easy adjustment of the blades. Drop forged, centre stop with extra-large shock-absorbing zone; painted tubular handles.

#### Application:

For cutting normal and high-tensile steels up to 48 HRC (about 1600 N/mm<sup>2</sup> tensile strength).

#### Material:

Special tool steel jaws, blades induction hardened.

#### Spare part:

Spare jaws No. 734110.

### Technical description

overall length	610 mm
for round steel bar up to 48 HRC and 1600 N/mm <sup>2</sup> up to Ø	7 mm
for round steel bar up to 19 HRC and 800 N/mm <sup>2</sup> up to Ø	9 mm
for round steel bar up to 40 HRC and 1200 N/mm <sup>2</sup> up to Ø	8 mm
Cutting capacity	<48 HR
with over-expansion guard	yes
Manufacturer's designation	UNIBOLT®
Blade	hardened
Material	Special tool steel

Surface	Painted red
with adjustment screw	yes
Type of product	Cutting pliers

---

## Accessories

Spare jaws complete with screws overall length 610 mm	734110 610
---	------------