



## Taper pin punches, special quality chrome-plated, Tip Ø: 8mm



### Order data

Order number	745300 8
GTIN	7610733005062
Item class	73B

### Description

**Version:**

Octagonal shank with conical shaft, through hardened. **Head specially annealed** to prevent splintering.

Highest possible tip hardness – approx. 59 HRC – with exceptional toughness.

**Material:**

Special quality of extra chrome vanadium steel, chrome-plated.

### Technical description

overall length	200 mm
Tip Ø	8 mm
Shank Ø	14 mm
Type of product	Drift punch