



Pin punch with handle, Tip Ø: 5mm



Order data

Order number	746940 5
GTIN	7610733254927
Item class	73B

Description

Version:

Sturdy octagonal shank with cylindrical shaft. Uniformly through hardened over the entire length. Head specially annealed to prevent splintering. Actual Ø 0.05 - 0.5 mm less than nominal Ø, prevents the pin punch jamming in the hole.

Material:

Special quality extra chrome vanadium steel (i.e. the highest possible peak hardness - approx. 59 HRC - combined with special toughness), chrome-plated. Hand grip with a non-allergenic elastomer coating.

Technical description

Pin length	72 mm
Tip Ø	5 mm
overall length	180 mm
Handle	Plastic handle with skin-friendly elastomer coating
Point hardness	59 HRC
Type of striking head	specially annealed
Material	Extra chrome vanadium steel, special quality
Surface	chrome-plated
Type of product	Parallel pin punches

