



Mechanic's pin punches, Point Ø D: 4mm



Order data

Order number	747500 4
GTIN	7610733200498
Item class	73B

Description

Version:

Round steel, exceptionally slim and handy. With knurled shank. Through hardened, **head specially annealed** to prevent splintering. Highest possible tip hardness (approx. 59 HRC) with exceptional toughness. Actual Ø 0.05 - 0.5 mm less than nominal Ø, prevents the pin punch jamming in the hole.

Material:

Extra chrome vanadium steel, surface chrome-plated.

Technical description

Shank Ø S	8 mm
overall length L ₁	115 mm
Point Ø D	4 mm
Mandrel length L ₂	30 mm
Point hardness	59 HRC
Type of striking head	head specially annealed
Material	Extra chrome vanadium steel
Surface	chrome-plated
Type of product	Parallel pin punches