



## Abrasive flap wheel roller, fabric, slit (A), Ø 100 × 100 mm, Grit: 120



### Order data

|              |               |
|--------------|---------------|
| Order number | 568466 120    |
| GTIN         | 4045197526717 |
| Item class   | 52E           |

### Description

#### Version:

**Flap strips of abrasive cloth** around the shank of the flap brush. Standard size **Ø 100×100 mm** or narrow version **Ø 100×50 mm** for grinding smaller areas. Mounting bore Ø 19 mm with multiple splines.

Abrasive cloth slit.

#### Application:

For **gentle longitudinal strokes** even on slightly convex surfaces, particularly versatile.

#### Note:

For matching the width of narrow rollers Ø 100×50 mm use the spacer ring pack No. 568439.

### Technical description

|   |                        |
|---|------------------------|
| recommended speed                       | 3700 min <sup>-1</sup> |
| Grit                                    | 120                    |
| Grinding media backing                  | Fabric                 |
| Grinding medium code                    | A                      |
| Iron, sulphur and chlorine constituents | < 0.1 %                |
| Roller Ø                                | 100 mm                 |

|                        |                                |
|------------------------|--------------------------------|
| Roller width           | 100 mm                         |
| Product name attribute | Ø 100 × 100 mm                 |
| Type of product        | Flap wheel roller fabric, slit |

## User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable                                  |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable only under restricted conditions |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable only under restricted conditions |                |          |
| GG(G)                          | suitable                                  |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable                                  |                |          |
| Wood                           | suitable                                  |                |          |
| Paint                          | suitable only under restricted conditions |                |          |
| dry                            | suitable                                  |                |          |