



## Pin punch, special quality powder-coated, Point Ø D: 6mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 746920 6      |
| GTIN         | 7610733243471 |
| Item class   | 73B           |

### Description

#### Version:

Sturdy octagonal shank with cylindrical shaft. Uniformly through hardened over the entire length. **Head specially annealed** to prevent splintering. Actual Ø 0.05 - 0.5 mm less than nominal Ø, prevents the pin punch jamming in the hole.

**Special quality**, i.e. highest possible tip hardness – approx. 59 HRC – with exceptional toughness.

#### Material:

Special quality, of extra chrome vanadium steel, chrome-plated and powder-coated.

### Technical description

|                               |  |
|-------------------------------|--|
| Mandrel length L <sub>2</sub> | 40 mm  |
| Point Ø D                     | 6 mm   |
| overall length L <sub>1</sub> | 150 mm   |
| Shank Ø S                     | 10 mm  |
| Point hardness                | 59 HRC   |
| Material                      | Special quality of extra chrome vanadium steel |
| Surface                       | chrome-plated, powder-coated                   |
| Type of product               | Parallel pin punches                           |

