


3M
Mini-linishing belt Ø 90×100 mm, 337DC, Grit: 120

Order data

Order number	568552 120
GTIN	4001895949050
Item class	53M

Description
Version:

Mini-belts Ø 90×100 mm (289×100 mm).

Defined blocks pressed in as abrasive grit. High grit density for very long working life. **No clogging** due to defined channels. **Consistent surface quality** over the entire grinding process, even on thin sheets.

Application:

For use on surface grinding and burnishing machines with backing rollers No. 568570 / 568575 (mounting bore Ø 19 mm). Maximum speed 5000 rpm.

Grinding medium code: A

Iron, sulphur and chlorine constituents: < 0.1 %

3M grit designation: A160

Technical description

Linishing belt width	100 mm
Grit	120
3M grit designation	A160
Linishing belt Ø	90 mm
Grinding medium code	A

Iron, sulphur and chlorine constituents	< 0.1 %
Manufacturer's designation	337DC

Accessories

Backing roller Ø 90×100 mm Type HARD	568580 HARD
Backing roller Ø 90×100 mm Type SOFT	568580 SOFT
Backing roller Ø 90×100 mm Type AIR	568580 AIR