



Measurement transducer, maximum torque: 20N·m



Order data

Order number	654255 20
GTIN	4018754224418
Item class	63B

Description

Version:

High accuracy due to measurement processing / digitising directly within the measurement transducer. Insensitive to lateral forces due to particularly flat form.

Suitable for:

Workshop torque analyser No. 654250.

Note:

Analysers and measurement transducers with other measuring ranges available on request.

Technical description

Weight	1.7 kg
Square socket	1/4 in
Measuring range	0.4 - 20 Nm
maximum torque	20 Nm
Direction of tightening	For right and left-hand tightening
Test certificate	Manufacturer's test certificate
Calibration	O4

Type of product

Torque testing device

ServicesCalibration clockwise / anti-clockwise Torque analyser /
sensor maximum torque 400/2 N·m

020140 400/2

DAkkS calibration clockwise / anti-clockwise Torque
analyser / sensor maximum torque 0,1-1100/2 N·m

020150 0,1-1100/2