

**Test pump "RP 50-S"****Order data**

Order number	814890
GTIN	4004625602003
Item class	86A

Description**Version:**

Sturdy sheet metal vessel with corrosion-proof coating and 12 litre volume. The pressure gauge has a fine scale and is graduated in international units (bar, psi, MPa). Memory pointer for easy determination of the pressure setting or pressure drop. Easy-acting force transfer to the pressure piston, using an ergonomic pump lever. Easy maintenance using a grease nipple. Measurement using a test hose armoured with steel braiding and R 1/2" connection.

Application:

Pressure testing to national and international guidelines of pipe work and pressure vessels, using oil or water (up to 60 bar).

Test and pressure range, with 20 psi graduation: 0 - 860 psi

Test and pressure range, with 1 bar graduation: 0 - 60 bar

Test and pressure range, with 0.1 MPa graduation: 0 - 6 MPa

Container length: 720 mm

Container width: 170 mm

Container height: 260 mm

Technical description

Container length	720 mm
Test and pressure range, with 1 bar graduation	0 - 60 bar

Container height	260 mm
Test and pressure range, with 0.1 MPa graduation	0 - 6 MPa
Suction volume per stroke	45 ml
Test and pressure range, with 20 psi graduation	0 - 860 psi
Container width	170 mm
Manufacturer's designation	RP 50-S
Type of product	Test pump