

3M Scotch-Brite™

Compact deburring wheel Rapid Cut (Cubitron™ II), RC-UW, Disc Ø×Width×Bore Ø: 152X25X25 mm

Order data

Order number	568725 152X25X25
GTIN	50051115667416
Item class	53M

Description

Version:

Fleece compact discs create a **reproducible finish**, since fresh grinding grit is continually being exposed. **No change in the workpiece geometry, no grinding groove formation, long working life.**

Compressed fibrous fleece with aggressive **Cubitron™ II ceramic grit.**

Application:

For **heavy deburring work** with significantly **increased metal removal rate** compared to rolled compact wheels. Very good edge stability.

On **bench grinders** or portable grinders with mandrel No. 556380 size 1–2 and reducer flange No. 568782. Suitable grinding wheel dresser No. 568785.

Grinding medium code: Ceramic

Bore Ø: 25 mm

Grit designation: extra coarse

Degree of hardness: hard

Width: 25 mm

Bore Ø: 25 mm

Version: 7C extra coarse

Technical description

recommended circumferential speed	m/s
Propulsive equipment	
suitable for quick-change system	
Adapter	
Shape description	
Iron, sulphur and chlorine constituents	%

Bonding	
Shape	
maximum circumferential speed	m/s
maximum speed	rpm
Backing pad	
Manufacturer's designation	RC-UW
Grinding media backing	
Product name attribute	RC-UW
optimised for material	
Type of product	