



HOLEX Pro INOX solid carbide milling cutter HPC, AlCrN, Ø f8 DC: 10mm

Order data

Order number	GG1021 10
GTIN	4045197908605
Item class	GGN

Description
Version:

For **outstanding tool life**. For use at **high cutting speeds**, particularly suitable even for steels up to approx. 1100 N/mm².

Same as No. 203021.

Technical description

Recess Ø D ₁	9.7 mm
Direction of infeed	horizontal, oblique and vertical
Corner chamfer width at 45°	0.2 mm
Feed f _z for side milling in INOX > 900 N/mm ²	0.045 mm
Cutting edge Ø D _c	10 mm
Shank	DIN 6535 HB to h6
Feed f _z for slot milling in stainless steel > 900 N/mm ²	0.04 mm
Flute length L _c	30 mm
Shank Ø D _s	10 mm

Overhang length L_1 incl. recess	38 mm
No. of teeth Z	4
Tolerance nominal \varnothing	f8
Overall length L	80 mm
Helix angle	35 degrees
Corner chamfer angle	45 degrees
Contents	5
Series	Pro Inox
Coating	AlCrN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Machining strategy	HPC
Colour ring	blue
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	240 m/min	P
Steel < 750 N/mm ²	suitable	220 m/min	P
Steel < 900 N/mm ²	suitable	180 m/min	P
Steel < 1100 N/mm ²	suitable	180 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	150 m/min	P

TOOLOX 33	suitable only under restricted conditions	115 m/min	H
TOOLOX 44	suitable only under restricted conditions	80 m/min	H
INOX < 900 N/mm ²	suitable	100 m/min	M
INOX > 900 N/mm ²	suitable	85 m/min	M
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable		
dry	suitable		
Air	suitable only under restricted conditions		

Accessories

HOLEX Pro INOX solid carbide milling cutterHPC Ø f8 DC
10 mm

203021 10