



HOLEX Pro INOX solid carbide milling cutter HPC, AlCrN, Ø f8 DC: 20mm

Order data

Order number	GG1021 20
GTIN	4045197908636
Item class	GGN

Description
Version:

For **outstanding tool life**. For use at **high cutting speeds**, particularly suitable even for steels up to approx. 1100 N/mm².

Same as No. 203021.

Technical description

Recess Ø D ₁	19.5 mm
Tolerance nominal Ø	f8
Feed f _z for slot milling in stainless steel > 900 N/mm ²	0.07 mm
Corner chamfer width at 45°	0.3 mm
Flute length L _c	60 mm
Overall length L	126 mm
Shank	DIN 6535 HB to h6
Direction of infeed	horizontal, oblique and vertical
No. of teeth Z	4

Shank $\varnothing D_s$	20 mm
Cutting edge $\varnothing D_c$	20 mm
Feed f_z for side milling in INOX > 900 N/mm ²	0.08 mm
Overhang length L_1 incl. recess	74 mm
Helix angle	35 degrees
Corner chamfer angle	45 degrees
Contents	5
Series	Pro Inox
Coating	AlCrN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Machining strategy	HPC
Colour ring	blue
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	240 m/min	P
Steel < 750 N/mm ²	suitable	220 m/min	P
Steel < 900 N/mm ²	suitable	180 m/min	P
Steel < 1100 N/mm ²	suitable	180 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	150 m/min	P

TOOLOX 33	suitable only under restricted conditions	115 m/min	H
TOOLOX 44	suitable only under restricted conditions	80 m/min	H
INOX < 900 N/mm ²	suitable	100 m/min	M
INOX > 900 N/mm ²	suitable	85 m/min	M
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable		
dry	suitable		
Air	suitable only under restricted conditions		

Accessories

HOLEX Pro INOX solid carbide milling cutter HPC Ø f8 DC
20 mm

203021 20