

Garant
Solid carbide mini milling cutter, AlCrN, Ø e8 DC: 2,5mm

Order data

Order number	GG1264 2,5
GTIN	4045197906953
Item class	GGN

Description
Version:

Shank similar to **DIN 6535 HB**. Improved coating for general-purpose applications in steel and cast iron.

Same as No. 202264.

Technical description

Shank form	HB
Feed f_z for side milling in steel $< 750 \text{ N/mm}^2$	0.011 mm
Shank	DIN 6535 HB to h6
Cutting edge $\varnothing D_c$	2.5 mm
Overall length L	45 mm
Flute length L_c	4 mm
No. of teeth Z	3
Shank $\varnothing D_s$	6 mm
Corner chamfer width at 45°	0.1 mm
Helix angle	45 degrees

Feed f_z for slot milling in steel < 750 N/mm ²	0.01 mm
Tolerance nominal \varnothing	e8
Direction of infeed	horizontal, oblique and vertical
Contents	5
Coating	AlCrN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Cutting width a_e for milling operation	$0.5 \times D$ for side milling
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable	280 m/min	N
Alu > 10% Si	suitable	200 m/min	N
Steel < 500 N/mm ²	suitable	120 m/min	P
Steel < 750 N/mm ²	suitable	110 m/min	P
Steel < 900 N/mm ²	suitable	100 m/min	P
Steel < 1100 N/mm ²	suitable	70 m/min	P
Steel < 1400 N/mm ²	suitable	60 m/min	P
INOX < 900 N/mm ²	suitable	70 m/min	M
INOX > 900 N/mm ²	suitable	50 m/min	M
GG(G)	suitable	90 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		

dry	suitable only under restricted conditions
Air	suitable

Accessories

Solid carbide mini milling cutter Ø e8 DC 2,5 mm	202264 2,5
--	------------