



Measurement transducer, maximum torque: 1100N·m



Order data

Order number	654255 1100
GTIN	4018754224425
Item class	63B

Description

Version:

High accuracy due to measurement processing / digitising directly within the measurement transducer. Insensitive to lateral forces due to particularly flat form.

Suitable for:

Workshop torque analyser No. 654250.

Note:

Analysers and measurement transducers with other measuring ranges available on request.

Technical description

Square socket	3/4 in
maximum torque	1100 Nm
Measuring range	25 - 1100 Nm
Weight	3.1 kg
Direction of tightening	For right and left-hand tightening
Test certificate	Manufacturer's test certificate
Calibration	O4

Type of product	Torque testing device
-----------------	-----------------------

Services

DAkS calibration clockwise / anti-clockwiseTorque analyser / sensor maximum torque 1000/2 N·m	020150 1000/2
---	---------------

Calibration clockwise / anti-clockwiseTorque analyser / sensor maximum torque 1000/2 N·m	020140 1000/2
--	---------------

Accessories

Square drive calibration adaptor Type 2	654383 2
---	----------

Square drive calibration adaptor Type 3	654383 3
---	----------

Square drive calibration adaptor Type 4	654383 4
---	----------