



Cutting disc STANDARD ** for stone, Disc Ø: 125mm



Order data

Order number	569700 125
GTIN	9003173677872
Item class	53T

Description

Version:

Universal stone cutting disc (specification: **C30-BF**).

Application:

For natural and synthetic stone, refractory stone, and concrete.

Technical description

Shape	42
Shape description	depressed centre
Bore Ø	22.23 mm
maximum speed	12200 min ⁻¹
Disc thickness	2.5 mm
Specification	C30-BF
Disc Ø	125 mm
for material thicknesses	7.5 mm

Grinding media	Silicon carbide (SiC)
Grinding medium code	SiC
optimised for material	Synthetic stone
optimised for material	Natural stone
optimised for material	Stone
Propulsive equipment	Angle grinders
maximum circumferential speed	80 m/s
Type of product	Cutting disc