

LESSMANN®
THE GERMAN BRUSH COMPANY
Burnishing brush Stainless steel wire 0.20 mm, Ø 100 × 70 mm

Order data

Order number	568435
GTIN	4017359203613
Item class	57L

Description
Version:

Dimension **Ø 100×70 mm**, bore Ø 19 mm with double spline.

Waved **stainless steel wire** with **high resistance** to corrosion, acids, alkalis and high temperatures. Ideal for burnishing stainless steel sheets.

Application:

On burnishing machines with spacer ring pack No. 568439.

Technical description

Bore Ø	19 mm
Bristle thickness	0.2 mm
Brush width	70 mm
Brush Ø D ₁	100 mm
Product name attribute	Ø 100 × 70 mm
Type of product	Burnishing brush

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
dry	suitable		

Accessories

Spacer ring set 6 pieces

568439