



Electronic torque analyser "TruCheck", maximum torque: 350 N·m

Order data

Order number	654470 350
GTIN	5060207560153
Item class	66D

Description

Version:

- **Compact, handy torque analyser.**
- **Screw attachment to a flat surface (table, wall etc.).**
- **Units of measure: N·m.**

Large easy to read LCD display.

Advantage:

- **Very easy to use (reduces errors).**
- **Suitable even for users who are not "Calibration Specialists".**
- **Only a single push button to zero the display.**

Application:

Setting and calibrating triggering torque wrenches.

Supplied with:

In a sturdy plastic case.

Direction of tightening: For right and left-hand tightening

Test certificate: Manufacturer's test certificate

Calibration: O4

Torque measuring accuracy: ± 1 %

Measuring range: 10 - 350 N·m

Display unit width: 150 mm

Display unit height: 145.5 mm

Display unit depth: 85 mm

Weight: 2.5 kg

Square socket: 1/2 inch

Technical description

Direction of tightening	For right and left-hand tightening
Power supply	

Test certificate	Manufacturer's test certificate
Norm	
Calibration	04
Interface	
Type of product	