



Combination spanner set, Number of keys: 13ZOLL



Order data

Order number	613510 13ZOLL
GTIN	4018754080892
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw width.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Ring end with **AS-Drive** profile. (Sizes 3.2 – 5 with hexagon).

Standard:

DIN 3113 A / ISO 3318 / ISO 7738

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Supplied with:

1 each combination spanner No. 613600 / 613500 / 613800 / 613900 / 613950 / 613520 / 613970: 1/4; 5/16; 3/8; 7/16; 1/2; 9/16; 5/8; 11/16; 3/4; 13/16; 7/8; 15/16; 1 inch

Note:

Advantage:

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

Technical description

Number of keys	13
Width across flats	imperial
Ring setting	15 degrees

Material	Chrome alloy steel
Surface	chrome-plated over nickel
Type of product	Spanner

Accessories

Combination spanner, imperial Width across flats 7/8 in	613520 7/8
Combination spanner, imperial Width across flats 15/16 in	613520 15/16
Combination spanner, imperial Width across flats 3/8 in	613520 3/8
Combination spanner, imperial Width across flats 13/16 in	613520 13/16
Combination spanner, imperial Width across flats 3/4 in	613520 3/4
Combination spanner, imperial Width across flats 9/16 in	613520 9/16
Combination spanner, imperial Width across flats 1/4 in	613520 1/4
Combination spanner, imperial Width across flats 1 in	613520 1
Combination spanner, imperial Width across flats 5/16 in	613520 5/16
Combination spanner, imperial Width across flats 5/8 in	613520 5/8
Combination spanner, imperial Width across flats 1/2 in	613520 1/2
Combination spanner, imperial Width across flats 11/16 in	613520 11/16
Combination spanner, imperial Width across flats 7/16 in	613520 7/16