

**Garant****Small pipe cutter universal****Order data**

Order number	818100
GTIN	4045197595638
Item class	81C

**Description****Version:**

Extremely sturdy design for very heavy duties. Clean and reliable cut thanks to 4 guide rollers in a row.

Die-cast magnesium body. With spare cutter wheel No. 818110.

**Advantage:**

Long working lives due to **TiN coated** cutter wheel. Saves effort and time due to:

- **Ergonomic handle**
- **Lightweight design**
- **Needle bearings on the guide rollers and cutter wheel**
- **Detachable manual deburrer with TiN-coated S20 blade.**

**Application:**

Multi-functional use for cutting stainless steel, aluminium, brass, and copper pipes.

**Technical description**

Cutter wheel bore	4.85 mm
Cutter wheel Ø	19 mm
Cutter wheel width	6.2 mm
for pipe outer Ø	3 - 35 mm
Weight	335 g
Length	165 mm

Width	65 mm
Height	40 mm
Number of guide rollers	4
Number of cutter wheels	1
suitable for pipe material	Brass
suitable for pipe material	Copper
suitable for pipe material	VA
suitable for pipe material	Aluminium
with ratchet function	no
Type of product	Pipe cutters

## Accessories

Stainless steel inner / outer deburrer for pipe Ø up to 35 mm	814920 35
Wheel pin	819630
Spare cutter wheel	818110
Guide roll set with needle bearings 16 pieces	818025