



## Combination spanner, imperial, Width across flats: 13/64in



### Order data

|              |               |
|--------------|---------------|
| Order number | 613520 13/64  |
| GTIN         | 4018754020065 |
| Item class   | 63A           |

### Description

#### Version:

Drop-forged. With close tolerance jaw width.

With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Ring end with **AS-Drive** profile. (Sizes 3.2 – 5 with hexagon).

#### Standard:

**DIN 3113 A / ISO 3318 / ISO 7738**

#### Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

#### Note:

**AS-Drive** – the special profile. An extremely accurately fitting profile - developed for aviation and aerospace. Tools with this profile can be recognised by the **AS-Drive** symbol. **Advantages:**

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

#### Advantage:

- **Bolts are gripped on the flanks. – The bolts are protected. – Longer bolt life.**
- **Larger contact surfaces between bolt and tool. – Secure grip and higher torque transmission.**

### Technical description

|                       |          |
|-----------------------|----------|
| Spanner length L      | 95 mm    |
| maximum jaw height h1 | 3 mm     |
| Width across flats    | 13/64 in |
| Width across flats    | imperial |

|                                 |            |
|---------------------------------|------------|
| maximum ring height $h_{2\max}$ | 3.2 mm     |
| Ring setting                    | 15 degrees |
| Type of product                 | Spanner    |