

**LESSMANN®**  
THE GERMAN BRUSH COMPANY**Wheel brush Steel wire 0.50 mm, Brush Ø D1× bore Ø d1 / thread M:  
178XM14mm****Order data**

Order number	571200 178XM14
GTIN	4017359016923
Item class	57L

**Description****Version:**

Straight round brush with smooth wire 0.50 mm, **knotted** and firmly crimped into the steel body. **Very aggressive brushing effect with high wear resistance.**

**Application:**

**Left knotted**, reliably avoids premature unwinding.

For heavy brush work, e.g. descaling, removing rust, removing paint, roughening, cleaning metal parts, also for cleaning formwork boards. With **internal thread M14**, for direct mounting **on angle grinders**.

**Technical description**

maximum speed	12500 min <sup>-1</sup>
Bristle thickness	0.5 mm
Number of twisted knots	32
Length of brush section H <sub>1</sub>	38 mm

Brush $\varnothing D_1$	178 mm
Bristle width $L_1$	14 mm
Thread M	M14
Brush material	Steel wire
Twisted knotting	left-hand plait
Type of product	Wheel brush