



**HOLEX Pro Steel solid carbide torus cutter HPC, TiAlN, Ø DC / R1: 5/1,0mm**

**Order data**

Order number	GG1357 5/1,0
GTIN	4045197909084
Item class	GGN

**Description**
**Version:**

Tolerance: Corner radius  $R_1 = \pm 0.03$  mm.

HPC milling cutters with various corner radii for all radial transitions.

Optimised flute form, eccentric relief ground, generous chip spaces.

**Same as No. 206357.**

**Technical description**

No. of teeth Z	4
Flute length $L_c$	13 mm
Overhang length $L_1$ incl. recess	17 mm
Cutting edge Ø $D_c$	5 mm
Overall length L	57 mm
Shank Ø $D_s$	6 mm
Recess Ø $D_1$	4.8 mm
Corner radius $R_1$	1 mm
Feed $f_z$ for slot milling in steel < 900 N/mm <sup>2</sup>	0.03 mm

Shank	DIN 6535 HB to h6
Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.04 mm
Helix angle	38 degrees
Contents	5
Series	Pro Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Tolerance nominal $\varnothing$	0 / -0.03
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Direction of infeed	horizontal, oblique and vertical
Cutting width $a_e$ for milling operation	0.3×D for side milling
Cutting width $a_e$ for milling operation	0.3×D for side milling
Machining strategy	HPC
Colour ring	green
Type of product	Torus cutter

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	260 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	240 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	160 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	80 m/min	M
GG(G)	suitable	250 m/min	K
Uni	suitable		

wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable
Air	suitable

---

## Accessories

HOLEX Pro Steel solid carbide torus cutterHPC Ø DC / R1  
5/1,0 mm

206357 5/1,0