

LESSMANN®
THE GERMAN BRUSH COMPANY**Deburring wheel brush Stainless steel wire 0.35 mm, Brush Ø D1× bristle width L1: 250X60mm****Order data**

Order number	570510 250X60
GTIN	4017359248423
Item class	57L

Description**Version:**

Bore diameter 50.8 mm with double keyway 13×7. Other bore diameters available.

Waved high-tensile **stainless steel wire**.

Application:

For all popular bench deburring machines. Particularly long working life due to special wire. Ideally suited for economical deburring of flat strips, profiles, pipes, fittings, plastic parts, and the like.

Note:

Only the tips of the bristles act on the workpiece. Excessive applied pressure does not improve the result, but increases the required drive power and reduces the working life of the brush.

Technical description

Brush width	58 mm
maximum speed	3600 min ⁻¹
Brush Ø D ₁	250 mm

Length of brush section H ₁	50 mm
Brush material	Stainless steel wire
Bristle thickness	0.35 mm
Propulsive equipment	Bench deburrer
Type of product	Wheel brush