

**Diamond cutting disc PREMIUM** Masonry cutter, Disc Ø: 125mm****Order data**

Order number	569770 125
GTIN	9003175980086
Item class	53T

Description**Version:**

Diamond cutting discs for wet and dry cutting. Bore Ø 22.23 mm.

- **High cutting performance of diamonds gives short cutting times.**
- **Extremely long working life, fewer disc changes.**
- **Unvarying diameter, always cuts to the full depth.**
- **Hardly any disc wear, reducing dust generation.**

Masonry cutting disc, cannot overheat, always replace in pairs.

Application:

For cutting all common building materials such as concrete (even reinforced), bricks, natural stone, tiles, ceramics, steel etc.

Material:

Optimised for: Concrete, bricks, porous concrete.

Note:

- **Diamond coating already pre-sharpened. Observe correct direction of rotation!**
- **Other diamond cutting discs on request.**

Technical description

Bore Ø	22.23 mm
Disc Ø	125 mm
maximum speed	12200 min ⁻¹
Grinding media	Diamond
Grinding medium code	D
optimised for material	Stone
Shape	41
Shape description	straight
Propulsive equipment	Angle grinder
maximum circumferential speed	80 m/s
Type of product	Cutting disc