



Electronic torque wrench / rotational angle wrench, maximum torque: 400N·m



Order data

Order number	655270 400
GTIN	4018754156528
Item class	63A

Description

Version:

- **Robust, compact body.**
- **Easy and flexible operation with menu selection on a large display.**
- **Recurrent screw settings can be collected on to a menu driven procedure.**
- **Especially large measuring range (5% – 100% of the nominal value).**
- **Adjustable early warning of the visual, tactile and acoustic signals.**
- **Resistant to oils, grease, fuel, brake fluid and Skydrol.**
- **Programmable using a PC.**
- **Easy to maintain due to simple adjustment.**
- **Integrated automatic reminder of calibration after the number of operations and elapsed time.**
- **Password protection against inadvertent change of settings and tampering.**
- **With 2 batteries (1.5 V mignon / AA / LR6).**
- **Torque and rotational angle both displayed at the same time.**
- **Convenient rotation angle measurement, no need for a reference arm.**
- **Easy input of reference: For plug-in heads with a different reference dimension, simply input the new dimension. No laborious calculations with formulae.**
- **QuickRelease: Secure fit and quick change for plug-in heads.**
- **Rotation angle measurement needs no reference arm.**
- **Easy to use: The arrow keys allow all functions to be selected. Clear and simple controls.**
- **Automatic reminder of calibration: After the number of operations and elapsed time.**
- **Warning signals: Warning signals can be selected as acoustic (buzzer), tactile (vibration in the handle), visual (LEDs and display) or any combination of these. The early warning point can be entered individually.**
- **Any point of application of force: The measurement remains precise in all cases, irrespective of where you grip the torque wrench.**
- **Data output: The USB interface allows the saved data to be exported and analysed via PC.**

- **Background illumination of the display for better legibility and evaluation of the screwing process (traffic light principle).**

The torque/rotational angle wrench offers easy and flexible operation with menu selection on a large display. Recurrent screw settings can be collected on to a menu driven procedure. The early warning of the **visual, tactile and acoustic** signals is adjustable. Resistant to oils, grease, fuel, brake fluid and Skydrol. The wrench is easy to maintain due to simple adjustment, can be programmed via a PC and offers a large measurement range. Password input ensures protection against unintentional adjustment and external access. Torque and rotational angle both displayed at the same time. Rotary angle measurement can be programmed easily, no reference arm required.

Units of measure: Nm, lbfft, lbfin.

Standard:

Tested to DIN EN ISO 6789.

Cutting dataa:

Legend for drawing and formula:

l_1 = Lever length without plug-in head

l_2 = Adjusted reference dimension on the torque wrench

l_3 = Lever length including factory calibration reference dimension

l_4 = Reference dimension of the plug-in head

L = Total length of the tool

T_1 = Torque to be set

T_2 = Specified torque

Supplied with:

Sturdy plastic box (size 400 in sturdy sheet metal box) and 2 batteries (1.5V mignon / AA / LR6).

Optional extras:

USB adapter, cable with latching plug and SENSOMASTER 4 software.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Weight	2330 g
Resolution	0.01 Nm
Packaging	sturdy plastic case
Socket for plug-in head	14×18 mm
maximum torque	400 Nm
Square drive	3/4 in
Torque measuring accuracy	±1 %
Exchangeable tool	Plug-in head

Data sheet

Torque range	20 - 400 Nm
Torque range	15 - 296 lbfft
#Article no of the battery / rechargeable battery fitted	081561 LR6
#Number of batteries contained	2
Torque range	180 - 3600 lbfin
Series	SENSOTORK® 713R
Measurement process	Torque
Measurement process	Rotation angle
Display	digital
Setting the trigger value	digital, adjustable
Overall length L	838 mm
Lever length including factory calibration reference dimension [I ₃]	775 mm
Lever length without plug-in head [I ₁]	750 mm
Feedback	displaying
Trigger principle	Vibration motor
Adjustable trigger value	adjustable
Standard	DIN EN ISO 6789
Reversible reading	Nm
Reversible reading	lbfin
Reversible reading	lbfft
Adjusted reference dimension on the torque wrench [I ₂]	25 mm
Connection format	for plug-in heads (rectangular socket)
Calibration	O3
Calibration	O5
Direction of tightening	For right- and left-hand tightening
Test certificate	Manufacturer's test certificate
Interface	USB interface
Measuring accuracy rotational angle	±1 %
Data can be recorded	yes

Measurement technology	electronic
Release signalling	optisk
Release signalling	akustisk
Release signalling	haptisk
Battery type	Mignon, AA
Power supply	Battery-powered
Type of product	Torque Wrench

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/655270-400>